

# Product data sheet

Specifications



## Light cross rails, PanelSeT SFN, Spacial SF, Spacial SM, W500mm, set of 2

NSYSLCR50

### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Light cross rail
Application	Multi-purpose
Nominal Dimensions Of The Housing	- W: 500 mm

### Complementary

Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX
Mounting Location	Between cross rails On structure of enclosure
Mounting Support	Adaptation profile, on SM enclosures
Device Composition	fixing elements 2 cross rails
Quantity Per Set	Set of 1
Material	Steel
Surface Finish	Zinc coated
Fixing Mode	By screws - screw type M6 self tapping
Adjustment	Adjustable with a pitch of 25 mm
Number Of Horizontal Rows	1
Height	30 mm
Width	450 mm fixing centers: 500 mm nominal: 410 mm useful:
Depth	18.6 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	5.0 cm
Package 1 Length	48.5 cm
Package 1 Weight	660.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	PAM
Number Of Units In Package 2	120
Package 2 Height	35.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	92.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations