

Product data sheet

Specifications

battery - 6 V - 1.5 Ah - Ni-Cd - in line

OVA51019E



Main

| | |
|---------------------------|----------|
| Product Or Component Type | Battery |
| Device Application | Lighting |
| Number Of Cells | 5 |
| Body Type | Sealed |

Complementary

| | |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range Compatibility | Exiway Exiway One emergency light fitting Exiway Exiway Plus emergency light fitting Exiway Luxa emergency light fitting Rilux Rilux emergency light fitting Exiway Maxi Slim emergency exit sign |
| Product Compatibility | Domina 11 W 1 h Exiway One 8/18/24 W Exiway Plus 8/18/24 W Universal Luxa 8 W 1 h/6 W 3 h Rilux 8 W 3 h |
| Battery Capacity | 1.5 Ah at 6 V, Ni-Cd (Nickel-Cadmium) |
| Battery Size | KRMT 23/43 |
| Operating Position | In line |
| Diameter | 23 mm |
| Length | 217 mm |
| Height | 26 mm |
| Width | 23 mm |
| Net Weight | 0.25 kg |

Environment

| | |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | -10...50 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.800 cm |
| Package 1 Width | 4.200 cm |
| Package 1 Length | 24.300 cm |
| Package 1 Weight | 236.000 g |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 30 |
| Package 2 Height | 15.000 cm |
| Package 2 Width | 30.000 cm |
| Package 2 Length | 40.000 cm |
| Package 2 Weight | 7.364 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

[Product Environmental Profile](#)