


# Product data sheet

Specifications



partition plate, Linergy TR terminals blocks, 2point, 2mm width, for screw terminals, blue

NSYTRAP22BL

⚠ Discontinued on: Aug 31, 2023

⚠ Discontinued

## Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Partition
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRV screw terminal - passthrough terminal block, length = 47.7 mm TRV screw terminal - protective earth terminal block, length = 47.7 mm TRV screw terminal - blade disconnect terminal block, length = 55 mm
Thickness	2 mm

## Complementary

Cable Cross Section	2.5 mm <sup>2</sup> 6 mm <sup>2</sup> 10 mm <sup>2</sup> 4 mm <sup>2</sup>
Number Of Connections	2
Number Of Measurement Input	1 2
Quantity Per Set	Set of 50
Net Weight	4.9 g
Colour	Blue

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	5 cm
Package 1 Length	5.5 cm
Package 1 Weight	4 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	50
Package 2 Height	4 cm
Package 2 Width	17 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	17 cm
Package 2 Weight	247 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	400
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	2.181 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)