

Product data sheet

Specifications



Component carrier, Linergy TR, for 5x20mm fuse, 6.2mm width, black

NSYTRASF520

Main

Range	Linergy
Product Name	TR
Product Or Component Type	Component carrier
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal - removable carrier disconnect terminal block TRR spring terminal - removable carrier disconnect terminal block TRP push-in - removable carrier disconnect terminal block
Length	28 mm
Thickness	6.2 mm

Complementary

Fuse Size	5 x 20 mm
Cable Cross Section	2.5 mm ² 4 mm ²
Number Of Connections	2 1
Number Of Terminals	2 3
Number Of Measurement Input	1 0
Mounting Mode	Plug-in
Quantity Per Set	Set of 10
Net Weight	3.85 g
Colour	Black

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	3.0 cm
Package 1 Length	3.7 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	10
Package 2 Height	2 cm
Package 2 Width	6 cm
Package 2 Length	10.5 cm
Package 2 Weight	40 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	1000
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.318 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)