

Product data sheet

Specifications



APC Audio-Video SurgeArrest 8 Outlets with Phone and Coax, 230V Germany

PF8T3V-GR

⚠ Discontinued on: Jan 4, 2022

⚠ Discontinued

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	230 V
Input Connection Type	Schuko CEE 7 / EU1-16P
Cable Length	3.05 m
Number Of Cables	1
Provided Equipment	1.8 m telephone cable User manual 60 cm coaxial cable

Physical

Colour	Silver
Height	37.2 cm
Width	12.2 cm
Depth	4.2 cm
Net Weight	1.26 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	50/60 Hz
Maximum Line Current	10 A

Output

Number Of Power Socket Outlets	8
Outlet Standard	Schuko CEE 7

Conformance

Product Certifications	CE
Equipment Protection Policy	Lifetime : 75000 euros

Environmental

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...50000 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0.00...15240.00 m
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Let Through Voltage Rating	700 V
Data Line Protected	1-4
Response Time	0 ns common mode
Common Mode Rejection	70 dB
Peak Current	30 kAcommon mode 40 kA per phase normal mode
Surge Energy Rate	2525 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	38.1 cm
Package 1 Width	21.6 cm
Package 1 Length	5.1 cm
Package 1 Weight	1.317 kg
Scs14	10731304243530

Contractual warranty

Warranty	5 years (all other countries), Lifetime (European Union countries only)
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
Environmental Disclosure		Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile		End of Life Information