

Product data sheet

Specifications



Pragma smoked door - for flush enclosure - 4 x 18 module

PRA99066

⚠ Discontinued on: Oct 31, 2023

⚠ Discontinued

Main

| | |
|------------------------------------|-----------------------|
| Range | Pragma |
| Product Or Component Type | Door |
| Accessory / Separate Part Category | Enclosure accessories |

Complementary

| | |
|---------------------------------|------------------------------------|
| Enclosure Mounting | Flush Surface |
| Key Number | Number to be stated |
| Type Of Front Cover | Transparent |
| Door Opening Side | Right or left |
| Number Of Horizontal Rows | 4 |
| 9 Mm Pitches | 36 |
| Number Of 18 Mm Modules Per Row | 18 |
| Total Number Of 18 Mm Modules | 72 |
| Installation Description | Surface mounting Flush mounting |
| Enclosure Material | Technoplastic |
| Width | 426 mm |
| Height | 750 mm |
| Depth | 20 mm |
| Colour | Smoked |

Environment

| | |
|---------------------------------------|-------------|
| Fire Resistance | 750 °C |
| Ip Degree Of Protection | IP40 |
| Ik Degree Of Protection | IK09 |
| Ambient Air Temperature For Operation | -25...60 °C |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Package 1 Height | 5.0 cm |
| Package 1 Width | 51.0 cm |
| Package 1 Length | 82.0 cm |
| Package 1 Weight | 2.048 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 36 |
| Package 2 Height | 118.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 85.73 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |