

Product data sheet

Specifications



New Unica - 1 x RJ45 socket - 2 m - Cat. 6 - STP - straight - shutter - white

NU541618F

⚠ Discontinued on: May 22, 2018

⚠ Discontinued

Main

Range	New Unica
Product Or Component Type	Data socket
Device Application	Communication
Device Presentation	Mechanism with fixing frame
Colour Tint	White (RAL 9003)
Data Socket Type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided Equipment	Protective flap Fixing frame Label holder

Complementary

Communication Network Type	1000BASE-TX
Communication Port Protocol	ATM 1200 Mbps
Number Of Modules	2 modules
Socket Number	1
Type Of Footprint	Infraplus
Connector Type	S-One
Cable Shielding Type	STP
Organization Of Wire	Shielded twisted pair
Connections - Terminals	Click
Device Mounting	Flush
Fixing Mode	Screws
Installation Direction	Straight
Material	Zamak: fixing frame Thermoplastic ABS-UV stabilised: central plate
Depth	40.5 mm
Width	74.5 mm
Height	74.5 mm
Embedding Depth	31.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Resistance To Chemical Agents	Resistant to alcohol (70 %)
	Resistant to alcohol (96 %)
	Resistant to A-Lactic Acid
	Resistant to diluted quaternary ammonium
	Resistant to diluted bleach
	Resistant to diluted ammonia
	Resistant to soapy water
	Resistant to crystal cleaner
	Resistant to hydrogen peroxide 10 volumes
	Resistant to hexane

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-25...55 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	4.1 cm
Package 1 Length	7.5 cm
Package 1 Weight	318 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)