

# Product data sheet

Specifications



## Decor - triple 2-way - complete product - 10 A 250 V - graphite

PRMS044023T

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Aesthetic Name	Decor
Product Or Component Type	Control switch
Device Presentation	Complete product
Type Of Packing	Flow-pack

### Complementary

Switch Function	Triple 2-way
Local Signalling	Without pilot light
[In] Rated Current	10 A
[Ue] Rated Operational Voltage	250 V AC
Material	ABS (acrylonitrile butadiene-styrene)
Number Of Modules	3
Embedding Depth	24.9 mm
Depth	33.9 mm
Length	123 mm
Height	9 mm
Width	85 mm
Connections - Terminals	Pillar terminals
Cable Cross Section	6 mm <sup>2</sup>
Awg Gauge	AWG 8
Fixing Mode	Clip-in

### Environment

Standards	ABNT NBR NM 60.669
-----------	--------------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	20.3 cm
Package 1 Length	25.9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	0.08 kg
------------------	---------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations