


Product data sheet

Specifications



Resi9 Pratic door 3x18 Modules

R9H18423P

⚠ Discontinued on: Jan 18, 2021

⚠ Discontinued

Main

| | |
|------------------------------------|---------------------|
| Range | Resi9 |
| Product Or Component Type | Door |
| Accessory / Separate Part Category | Enclosure accessory |
| Range Compatibility | Resi9 enclosure |

Complementary

| | |
|---------------------------------|---|
| Type Of Front Cover | Opaque (pratic) |
| Number Of Horizontal Rows | 3 |
| 9 Mm Pitches | 36 |
| Number Of 18 Mm Modules Per Row | 18 |
| Total Number Of 18 Mm Modules | 54 |
| Provided Equipment | 3 magnet 1 whiteboard marker 3 keyholder |
| Standards | IEC 61439-3 IEC 61439-1 IEC 60670-1-24 |
| Fire Resistance | 750 °C conforming to EN/IEC 60695-2-11 |
| Ip Degree Of Protection | IP40 conforming to EN/IEC 60529 |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 IK08 conforming to EN 50102 |
| Net Weight | 850 g |
| Width | 352.5 mm |
| Height | 495.5 mm |
| Depth | 27 mm |
| Colour Tint | White (RAL 9003) |

Environment

| | |
|---------------------------------------|-------------|
| Ambient Air Temperature For Operation | -15...60 °C |
|---------------------------------------|-------------|

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|---------|
| Package 1 Height | 3.3 cm |
| Package 1 Width | 36.5 cm |
| Package 1 Length | 51 cm |
| Package 1 Weight | 1.07 kg |

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

| | |
|--|---|
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |