

# Product data sheet

Specifications



## Exiway One - emergency light block - addressable - maintained - 2 h - 260 lm

OVA34343

 **Discontinued on:** Feb 22, 2021

 **Discontinued**

### Main

Range	Exiway
Product Name	Exiway One
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Addressable
Operational Mode	Maintained
Number Of Batteries	1 x 6 V 2.5 Ah Ni-Cd (Nickel-Cadmium)
Light Source	LED 24 W
Light Source Colour	White
Cover Type	Transparent
Wiring Device Additional Information	Can be inhibited with rest mode via Dardo Plus control unit

### Complementary

Range Compatibility	Dardo Plus control unit
[Ue] Rated Operational Voltage	220...230 V AC/DC 50 Hz
Power Consumption In Va	5.6 VA non-maintained 14 VA maintained
Power Consumption In W	1.5 W non-maintained 6.7 W maintained
Current Consumption	24 mA
Electrical Insulation Class	Class II
Autonomy	2 h
Charging Time	24 h
Type Of Glass	Fresnel glass
Device Mounting	Surface ceiling Hanging ceiling Flush false ceiling Flush wall Surface wall Electrified track
Material	Housing: plastic Cover: plastic
Height	146 mm
Depth	62 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	300 mm
-------	--------

## Environment

Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK07
Fire Resistance	850 °C
Product Certifications	IMQ AENOR ENEC
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15 cm
Package 1 Width	7.3 cm
Package 1 Length	30.6 cm
Package 1 Weight	1.14 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>