

# Product data sheet

Specifications



## Astro Guida - emergency exit sign - standard - maintained - 3 h

OVA38465E

⚠ Discontinued on: Feb 22, 2021

⚠ Discontinued

### Main

Range	Exiway
Product Name	Astro Guida
Product Or Component Type	Emergency exit sign
Device Application	Signalling
Function	Standard
Supply	Maintained
Colour	White
Light Source Colour	White
Provided Equipment	5 pictogram stickers bracket flag installation
Cover Type	Transparent

### Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	200...230 V AC/DC 50 Hz
Power Consumption In Va	12 VA
Current Consumption	52 mA
Electrical Insulation Class	Class II
Battery Capacity	1.5 Ah at 4.8 V, Ni-Cd (Nickel-Cadmium)
Autonomy	3 h
Charging Time	24 h
Bulb Type	Cold cathode light 40000 h
Luminous Flux	Maintained mode: 40 lm Emergency condition: 25 lm
Visibility Distance	24 m
Indicator Type	Indicator two sides
Material	Plastic: housing Plastic: cover
Device Mounting	Surface ceiling Hanging ceiling Surface wall Electrified track Flag type bracket wall
Height	213 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	261 mm
Depth	35 mm
Net Weight	0.865 kg

## Environment

Ip Degree Of Protection	IP42
Ik Degree Of Protection	IK06
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	IEC 50-11 EN 60695-2-10 IEC 695-2-1 EN 1838 EN 60598-2-22

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	28 cm
Package 1 Length	28.5 cm
Package 1 Weight	907 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>