


Product data sheet

Specifications



Emergency luminaire, Exiway Smartbeam Activa, flush, escape, 1.5 h

OVA48920

⚠ Discontinued on: Jan 11, 2023

⚠ Discontinued

Main

Range	Exiway
Product Name	Exiway Smartbeam Activa
Product Or Component Type	Emergency luminaire
Device Application	Lighting
Function	Self-test
Operational Mode	Maintained Non-maintained
Number Of Batteries	1 x 3.2 V 1.5 Ah LiFePO4
Light Source	1 x LED 10 W

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Power Consumption In Va	3.9 VA non-maintained 8.3 VA maintained
Power Consumption In W	0.43 W non-maintained 3.5 W maintained
Electrical Insulation Class	Class II
Led Lifespan	100000 h
Test Function	Automatic periodical functional & duration test
Autonomy	1.5 h
Charging Time	12 h
Illuminance	1 lux
Device Mounting	Flush false ceiling
Material	Thermoplastic self-extinguishing
Height	Driver: 55.8 mm
Depth	Driver: 23.8 mm Light fitting: 31.5 mm
Width	Driver: 256.6 mm
Diameter	90 mm light fitting:
Net Weight	292 g

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	Light fitting: IP42 Driver: IP20
Ik Degree Of Protection	IK04
Flame Retardance	V2
Fire Resistance	850 °C
Product Certifications	ENEC CE
Ambient Air Temperature For Operation	0...40 °C
Standards	EN 60598-1 EN 62034 UL 94 EN 60598-2-22 EN 62471: group 1 EN 60695-2-10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	27.8 cm
Package 1 Length	18.2 cm
Package 1 Weight	388.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information