

# Product data sheet

Specifications



## Miluz - power brazilian socket-outlet - assembled (PS) - 10 AX - 250 V - white

S3B60340

### Main

Range	Miluz
Aesthetic Name	Bossa
Product Or Component Type	Socket-outlet
Fixing Mode	By screws

### Complementary

Device Presentation	Complete mechanism
Outlet Standard	Brazilian
Type Of Packing	Flow-pack
[In] Rated Current	10 A
[Ue] Rated Operational Voltage	250 V AC
Material	ASA + PC: wiring device
Number Of Modules	1 module
Connections - Terminals	Screw-clamp terminals
Cable Cross Section	4 mm <sup>2</sup>
Awg Gauge	AWG 12
Height	111 mm
Width	73 mm
Depth	40 mm
Embedding Depth	30.5 mm
Projecting Depth	9.5 mm

### Environment

Standards	ABNT NBR 14.136 ABNT NBR NM 60.884
-----------	---------------------------------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.1 cm
Package 1 Width	11.5 cm
Package 1 Length	7.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	54 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	15.8 cm
Package 2 Width	21.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	1289 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations