

Product data sheet

Specifications



Pragma flush enclosure - IP 40 - 1 x 13 modules - transparent door

PRA23113

⚠ Discontinued on: Mar 23, 2020

⚠ End-of-service on: Feb 3, 2022

⚠ Discontinued

Main

Range	Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Width	366 mm wall: 396 mm outside:
Height	330 mm wall: 360 mm outside:
Depth	41 mm outside: 86 mm wall:
Nb Of 18 Mm Modules Per Row	13
Nb Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Provided Equipment	2 x terminal block 1 x identification label 1 x marking kit 1 x blanking plate strip
Type Of Door	Transparent

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	26
Total Number Of 18 Mm Modules	13
Power Dissipation In W	34 W
[In] Rated Current	63 A
Type Of Rail	DIN
Cable Entry	Side pre-cutouts Cable or tube Removable plates
Number Of Terminal Blocks	1 earth (Quick) with 13 outgoers 1 neutral (Quick) with 11 outgoers
Distribution Block Outgoers	1 x 25 mm² for earth 12 x 6 mm² for earth 3 x 25 mm² for neutral 8 x 6 mm² for neutral
Enclosure Material	Back part: technoplastic Door: technoplastic Front face: technoplastic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Enclosure: white (RAL 9016) Front face: grey (RAL 7004) Door: colourless
--------	--

Environment

Fire Resistance	Front face: 750 °C conforming to IEC 60695-2-1 Back part: 850 °C conforming to IEC 60695-2-1 Door: 650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP30 without door conforming to EN/IEC 60529 IP40 with door conforming to EN/IEC 60529
Ik Degree Of Protection	IK08 without door conforming to EN/IEC 62262 IK09 with door conforming to EN/IEC 62262
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C
Standards	IEC 62262 IEC 60439-3 IEC 60695-2-11 EN 60695-2-11 IEC 60947-7-1 EN 60439-3 IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	42 cm
Package 1 Length	38 cm
Package 1 Weight	3.11 kg

Contractual warranty

Warranty	18 months
----------	-----------