

# Product data sheet

Specifications



Swith, Miluz, Bossa, 1-way + 2-way, assembled (PS), 10AX 250V, white

S3B62090

## Main

Range	Miluz
Aesthetic Name	Bossa
Product Or Component Type	Switch

## Complementary

Device Presentation	Complete mechanism
Type Of Packing	Flow-pack
Switch Function	1-way + 2-way switch
Local Signalling	Without pilot light
Marking	1 - L 1 - 2 - L
[In] Rated Current	10 A
[Ue] Rated Operational Voltage	250 V AC
Material	ABS (acrylonitrile butadiene-styrene): wiring device
Number Of Modules	2 modules
Fixing Mode	By screws
Connections - Terminals	Screw-clamp terminals
Cable Cross Section	4 mm <sup>2</sup>
Awg Gauge	AWG 12
Height	111 mm
Width	73 mm
Depth	36 mm
Embedding Depth	26 mm
Projecting Depth	10 mm

## Environment

Standards	ABNT NBR NM 60.669
Product Certifications	NOM/ANCE RETIE

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4 cm
Package 1 Width	11.5 cm
Package 1 Length	7.7 cm
Package 1 Weight	69 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	15.8 cm
Package 2 Width	21.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	1589 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations