

# Product data sheet

Specifications



## Cover frame, Orion, with fixing frame, 3 modules, white, IP55

S731103554

### Main

Range	Orion
Product Or Component Type	Cover frame

### Complementary

Device Mounting	Flush
Provided Equipment	Fixing frame
Number Of Gangs	1 gang
Installation Direction	Horizontal Vertical
Number Of Modules	3 modules
Fixing Mode	Screws
Colour Tint	White (RAL 9003)
Surface Finish	Glossy
Surface Treatment	Untreated
Type Of Packing	Flow-pack
Quantity Per Set	Set of 10
Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Material	Thermoplastic ABS-UV stabilised: cover frame Thermoplastic ABS-UV stabilised: fixing frame PVC (polyvinyl chloride): front EPDM: gasket
Height	90 mm
Width	126 mm
Depth	29 mm
Net Weight	0.081 kg
Standards	EN 60669-1
Product Certifications	INMETRO

### Environment

Ik Degree Of Protection	IK01
Ip Degree Of Protection	IP55

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	Petrol
	Hydrogen peroxide (H2O2)
	UV resistant
	Alcohol
	Oil
	Acetone
	Window-cleaning fluid
	Liquid soap
	Bleach

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	9.3 cm
Package 1 Length	20 cm
Package 1 Weight	15 g

# Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	