

Product data sheet

Specifications



Orion - cover-frame 4X4 - 6 modules - white / aluminium orbital blue

S733203619

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

| | |
|---------------------------|---------------------------|
| Range | Orion |
| Aesthetic Name | Orion materials aluminium |
| Product Or Component Type | Cover frame |

Complementary

| | |
|---------------------------------------|------------------------------------------------------------|
| Device Mounting | Flush |
| Number Of Gangs | 1 gang |
| Number Of Modules | 6 modules |
| Fixing Mode | Clip-in |
| Colour Tint | White (RAL 9003) Aluminium orbital blue (Pantone 629C) |
| Surface Finish | Metallic |
| Surface Treatment | Metallic |
| Type Of Packing | Blister |
| Quantity Per Set | Set of 10 |
| Ambient Air Temperature For Storage | -5...50 °C |
| Ambient Air Temperature For Operation | -5...35 °C |
| Material | Thermoplastic ABS-UV stabilised: decorative frame Metal |
| Height | 120 mm |
| Width | 127.5 mm |
| Depth | 8.3 mm |
| Net Weight | 0.031 kg |

Environment

| | |
|-------------------------|-------|
| Ik Degree Of Protection | IK07 |
| Ip Degree Of Protection | IP21D |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|--------------------------|
| Environmental Characteristic | Petrol |
| | Acetone |
| | UV resistant |
| | Oil |
| | Bleach |
| | Liquid soap |
| | Alcohol |
| | Hydrogen peroxide (H2O2) |
| | Window-cleaning fluid |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 0.9 cm |
| Package 1 Width | 15 cm |
| Package 1 Length | 17 cm |
| Package 1 Weight | 64 g |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 16 cm |
| Package 2 Width | 15.2 cm |
| Package 2 Length | 25.9 cm |
| Package 2 Weight | 635 g |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope
