


# Product data sheet

Specifications



## Séquence5 - dolly switch - double 2-way - 10 AX - Brushed Gold

S800224C

 **Discontinued on:** Sep 30, 2021

 **Discontinued**

### Main

Range Of Product	Sequence5
Product Or Component Type	Switch
Device Presentation	Complete product
Switch Additional Information	With internal power connection
Switch Application	On/off switching
Type Of Packing	Box
Quantity Per Set	Set of 1
Sale Per Indivisible Quantity	1

### Complementary

Device Mounting	Flush
Switch Function	2-way
Number Of Rocker	2
Actuator	Small dolly rocker
Fixing Mode	By screws
Colour Tint	Brushed gold
Surface Finish	Glossy
Rated Current	10 AX at 250 V AC 50 Hz
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un with cos $\varphi$ = 0.3
Service Life In Cycles	20000 cycles at ON and OFF at rated voltage with cos $\varphi$ = 0.6
Electrical Durability	20000 cycles at ON and OFF at rated voltage with cos $\varphi$ = 0.6
Number Of Terminals	3 screwless terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> for rigid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for flexible cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for stranded cable(s)
Wire Stripping Length	12 mm
Material	Metal
Height	80 mm
Width	160 mm
Depth	49 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	35 mm
Net Weight	0.47 kg

## Environment

Ambient Air Temperature For Storage	-5...50 °C
Dielectric Strength	2000 V
Ambient Air Temperature For Operation	5...35 °C
Standards	2006/95/EEC EN 60669-1
Product Certifications	LCIE: CCA-FR_598285B LCIE: NF 604950 NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP21D
Environmental Characteristic	Acetone Bleach Petrol Liquid soap Alcohol Window-cleaning fluid Oil UV resistant

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	12 cm
Package 1 Length	18 cm
Package 1 Weight	525 g

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information