



# Product data sheet

Specifications



## Sedna - hotel card switch - 10AX without frame white

SDN1900121

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

### Main

Range	Sedna
Function	Card switch
Device Application	Control
Delivery Form	Without frame

### Complementary

Function	Hotel card switch
Power Range	2300 W
Rated Current	10 AX at 250 V AC
Kind Of Terminals	Screwless terminals
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Flexible Rigid
Wire Stripping Length	13 mm
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Fixing Mode	Claws, span of claws working range: 51...70 mm Screws
Height	75 mm
Width	71 mm
Depth	55 mm
Depth Of Visual Part	31 mm
Net Weight	0.063563 kg

### Environment

Ip Degree Of Protection	IP20
Conformity Mark	CE
Product Certifications	GOST-R

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.000 cm
Package 1 Width	7.000 cm
Package 1 Length	9.500 cm
Package 1 Weight	70.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	646.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	8.403 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations