

Product data sheet

Specifications



Sedna-double socket outlet with pin earthtwo frame-16A aluminium, PL std

SDN2801960

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

Main

Range	Sedna
Product Or Component Type	Socket-outlet
Outlet Standard Description	Pin earth
Device Application	Power supply
Delivery Form	Without frame
Outlet Standard	Poland
Rated Current	16 A at 250 V AC
Cover Plate Color	Aluminium
Kind Of Terminals	Lift terminals

Complementary

Installation	Flush
Power Range	3680 W
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Rigid Solid stranded Flexible
Wire Stripping Length	13 mm
Material Of Visible Parts	ASA + PC
Surface Finish	Glossy
Fixing Mode	Screws or claws 52...69 mm
Height	83 mm
Width	71 mm
Depth	48 mm
Depth Of Visual Part	23.8 mm
Net Weight	0.082 kg

Environment

Product Certifications	B
Ip Degree Of Protection	IP20

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	10.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	95.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	10.200 cm
Package 2 Width	20.500 cm
Package 2 Length	31.500 cm
Package 2 Weight	887.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.734 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations