


Product data sheet

Specifications



Sedna - TV connector - 1dB cream

SDN3200223

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

Range Name	Sedna
Function	TV socket
Tv Socket Type	End-of-line (terminal socket)
Delivery Form	Complete product
Cover Plate Color	Cream
Type Of Packing	Blister

Complementary

Number Of Outputs	1
Tv Connector Type	1 male IEC 9.52 mm
Installation	Flush
Kind Of Terminals	Glossy
Material Of Visible Parts	ASA + PC
Fixing Mode	Screws or claws, span of claws working range: 50...70 mm
Attenuation	1 dB
Connections - Terminals	Screw
Height	80 mm
Width	85 mm
Depth	40 mm
Depth Of Visual Part	14.6 mm
Net Weight	0.075 kg

Environment

Conformity Mark	CE
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	11.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	15.000 cm
Package 1 Weight	95.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.500 cm
Package 2 Width	20.500 cm
Package 2 Length	31.000 cm
Package 2 Weight	904.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.921 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations