

Product data sheet

Specifications



APC Replacement Battery Cartridge #32 with 2 Year Warranty

RBC32

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Product Or Component Type	Replacement battery cartridge
Battery Type	Lead-acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

Batteries & Runtime

Battery Location	Internal battery
Number Of Battery Blocks Per String	2
Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cabinet
Battery Voltage	24 V
Number Of Battery Replacement Quantity	1

Physical

Colour	Charcoal
Height	19.7 cm
Width	14.9 cm
Depth	6.4 cm
Net Weight	5.33 kg
Mounting Mode	Not rack-mountable

Output

Battery Capacity	7.0 Ah
------------------	--------

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...50000 ft
Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	0...40 °C
Storage Altitude	0.00...3048.00 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.5 cm
Package 1 Width	10.2 cm
Package 1 Length	22.9 cm
Package 1 Weight	5.91 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov