

Product data sheet

Specifications



Miluz-Bossa- duplex American socket outlet 2P+E 15A 120/125/127V~ GFCI with fixing frame white

S3B10300

! Discontinued

! Discontinued on: Jun 7, 2023

Main

Range	Miluz
Product Or Component Type	Socket-outlet
Fixing Mode	By screws

Complementary

Device Presentation	Mechanism with fixing frame
Outlet Standard Description	GFCI
Device Mounting	Flush
Outlet Standard	American
Type Of Packing	Flow-pack
[In] Rated Current	15 A
[Ue] Rated Operational Voltage	120/127 V AC 125 V AC
Material	PC (polycarbonate) FR: casing PC (polycarbonate) FR: centre plate ABS (acrylonitrile butadiene-styrene): adaptor frame ABS (acrylonitrile butadiene-styrene): cover frame
Surface Finish	Glossy
Number Of Modules	3 modules
Connections - Terminals	Screw-clamp terminals
Cable Stiffness	Rigid Stranded Flexible
Cable Cross Section	1.5...4 mm²
Awg Gauge	AWG 12 AWG 14
Height	115 mm
Width	73 mm
Depth	39.5 mm
Embedding Depth	30.4 mm
Projecting Depth	9 mm

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 94
	UL 943
	UL 498
	NMX J-508 ANCE
Product Certifications	NOM
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	5.2 cm
Package 1 Length	7.7 cm
Package 1 Weight	177 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	15.8 cm
Package 2 Width	21.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	1062 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations