


# Product data sheet

Specifications



## Sedna - roller blind pushbutton - 10A electric lock, without frame graphite

SDN1300170

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

### Main

Range Name	Sedna
Range	Sedna
Product Or Component Type	Push-button
Function	Roller blind
Delivery Form	Without frame
Marking	UP-DOWN
Kind Of Terminals	Screwless terminals

### Complementary

Interlocking Type	Electrical
Power Range	2300 W
Rated Current	10 AX at 250 V AC
Terminal Capacity	2 cable(s) 2.5 mm²
Wire Structure	Flexible Rigid
Wire Stripping Length	13 mm
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Surface Finish	Glossy
Fixing Mode	Claws, span of claws working range: 51...70 mm Screws
Height	71 mm
Width	71 mm
Depth	37 mm
Depth Of Visual Part	12 mm
Net Weight	0.061972 kg

### Environment

Conformity Mark	CE
Product Certifications	GOST-R
Ip Degree Of Protection	IP20

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	4.2 cm
Package 1 Length	7.1 cm
Package 1 Weight	74 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	120
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	9354 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1440
Package 3 Height	135 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	161.664 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations