

Product data sheet

Specifications



Sedna - single socket outlet, pin earth - 16A IP44 shutters, lid, white

SDN2890321

 **Discontinued on:** Dec 30, 2023

 **Discontinued**

Main

| | |
|-----------------------------|-------------------|
| Range | Sedna |
| Product Or Component Type | Socket-outlet |
| Outlet Standard Description | Pin earth |
| Delivery Form | Complete product |
| Additional Features | Lid and shuttered |
| Rated Current | 16 A at 250 V AC |
| Cover Plate Color | White |
| Kind Of Terminals | Lift terminals |

Complementary

| | |
|---------------------------|--------------------------------|
| Installation | Flush |
| Power Range | 3680 W |
| Terminal Capacity | 2 cable(s) 2.5 mm ² |
| Wire Structure | Flexible Rigid |
| Wire Stripping Length | 13 mm |
| Material Of Visible Parts | ASA + PC |
| Surface Finish | Glossy |
| Fixing Mode | Screws or claws 52...69 mm |
| Height | 85 mm |
| Width | 85 mm |
| Depth | 46.3 mm |
| Depth Of Visual Part | 18 mm |
| Net Weight | 0.095496 kg |

Environment

| | |
|-------------------------|------|
| Product Certifications | B |
| Ip Degree Of Protection | IP44 |

Packing Units

| | |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.000 cm |
| Package 1 Width | 11.000 cm |
| Package 1 Length | 15.000 cm |
| Package 1 Weight | 110.800 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 6 |
| Package 2 Height | 10.000 cm |
| Package 2 Width | 20.000 cm |
| Package 2 Length | 31.000 cm |
| Package 2 Weight | 788.000 g |
| Unit Type Of Package 3 | S04 |
| Number Of Units In Package 3 | 30 |
| Package 3 Height | 30.000 cm |
| Package 3 Width | 40.000 cm |
| Package 3 Length | 60.000 cm |
| Package 3 Weight | 4.287 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |