


Product data sheet

Specifications

encoder interface card, Altivar, with open collector outputs, 15V DC



VW3A3404

 To be discontinued on: Dec 31, 2024

 To be discontinued

Main

Range Of Product	Altivar
Product Or Component Type	Encoder interface card
Range Compatibility	Altivar 61 Altivar Process Modular Altivar 71Q Altivar 61Q Altivar 71 Altivar Lift
Discrete Output Type	Open collector
[Us] Rated Supply Voltage	15 V DC (voltage limits: 15...16 V)
Number Of Pulses Per Revolution	10000 for ATV71H.....383 5000 for all ATV61 drives 5000 for ATV71H...M3 5000 for ATV71H...M3X 5000 for ATV71H...N4

Complementary

Maximum Supply Current	0.175 A
Protection Type	Overload protection Short-circuit protection
Maximum Cable Distance Between Devices	500 m
Maximum Operating Frequency	300 kHz
Input Signal	A B Compliment of A Compliment of B/AB/A
Input Impedance	1 kOhm
Electrical Connection	Terminal, connection capacity: 0.2 mm ² (AWG 24) <100 m cable length, encoder, 100 mA at 10 V Terminal, connection capacity: 0.2 mm ² (AWG 24) <100 m cable length, encoder, 175 mA at 10 V Terminal, connection capacity: 0.2 mm ² (AWG 24) <200 m cable length, encoder, 100 mA at 10 V Terminal, connection capacity: 0.2 mm ² (AWG 24) <200 m cable length, encoder, 175 mA at 10 V Terminal, connection capacity: 0.5 mm ² (AWG 20) <500 m cable length, encoder, 100 mA at 10 V Terminal, connection capacity: 0.5 mm ² (AWG 20) <500 m cable length, encoder, 175 mA at 10 V
Net Weight	0.2 kg

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	17.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	150.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.470 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov