

Product data sheet

Specifications



2 Socket-outlet, Exxact, mechanism with fixing frame, 2P + E, 16A, Schuko, with shutter, screwless terminals anthracite

WDE003584

Main

| | |
|--------------------------------|-----------------------------|
| Range | Exxact |
| Product Or Component Type | Socket-outlet |
| Device Application | Power supply |
| Device Presentation | Mechanism with fixing frame |
| Socket Number | 2 |
| Outlet Standard | CEE 7/3 |
| Outlet Standard | Schuko |
| [Ue] Rated Operational Voltage | 250 V |
| Network Type | AC |
| Colour Tint | Anthracite (RAL 7021) |
| Quantity Per Set | Set of 5 |

Complementary

| | |
|------------------------------|---|
| Device Mounting | Flush |
| Outlet Poles Configuration | 2P + E |
| Rated Current | 16 A |
| Cover Type | With shutter |
| Fixing Mode | By claw kit |
| Connections - Terminals | Screwless terminals |
| Number Of Loop Terminals | 2 |
| Clamping Connection Capacity | 1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s) |
| Material | ASA + PC |
| Depth | 44.2 mm |
| Embedding Depth | 32.4 mm |
| Height | 88.1 mm |
| Width | 71 mm |
| Projecting Depth | 11.8 mm |

Environment

| | |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------|----------------|
| Standards | IEC 60884-1 |
| | SS 4280834 |
| | SFS 5610:2004 |
| | DIN VDE 0620-1 |
| Product Certifications | SEMKO |
| | FIMKO |
| | NEMKO |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.7 cm |
| Package 1 Width | 8.8 cm |
| Package 1 Length | 1.2 cm |
| Package 1 Weight | 81.3 g |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 26.0 cm |
| Package 2 Width | 10.1 cm |
| Package 2 Length | 9.3 cm |
| Package 2 Weight | 460.5 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging Transparency RoHS/REACH

Resource performance

✓ Sustainable Packaging

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |