

Product data sheet

Specifications

Thermostat, Exxact KNX, aluminium



WDE004963

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Exxact
Product Or Component Type	Thermostat

Complementary

Device Presentation	Mechanism with fixing frame
Device Application	Room
Technology Type	Electromechanical
Product Specific Application	Heating
Colour	Metallic
Quantity Per Set	Set of 1
Wiring Device Additional Information	Possibility to connect external sensor
[Ue] Rated Operational Voltage	5 V DC
[In] Rated Current	0.8 mA (resistive load)
Control Type	Knob
Function Available	Possibility to connect external sensor
Local Signalling	LED (red) for heating application
Connections - Terminals	Screw terminals
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	ABS (acrylonitrile butadiene-styrene)
Device Mounting	Flush
Fixing Mode	By screws

Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK02

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	7.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	119.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations