

Product data sheet

Specifications



Double USB charger, Exxact, 2.1A, metallic BP

WDE008762

⚠ Discontinued on: Dec 31, 2022

⚠ End-of-service on: Feb 6, 2023

⚠ Discontinued

Main

Range Of Product	Exxact
Product Or Component Type	USB charger
Device Application	Charger
Device Presentation	Complete product
Type Of Usb Power Supply	USB type A + A
Number Output Current	2.1 A
Colour Tint	Metallic

Complementary

Device Mounting	Flush
Quantity Per Set	1 piece
[Ue] Rated Operational Voltage	100...240 V AC +/- 10 % at 50/60 Hz
[In] Rated Current	180 mA
Energy Efficiency Ratio	72
Power Consumption In W	0.1 W
Nominal Output Power	10.5 W
Input Power	12 W
Integrated Connection Type	2 USB type A 5 V DC, maximum load current: 2.1 A
Service Life In Hours	30000 h 10.5 W
Number Of Terminals	2 screw terminals
Shape Of Screw Head	Pozidriv No 1
Clamping Connection Capacity	1.5...2.5 mm² for rigid cable(s) 1.5...2.5 mm² for flexible cable(s) 1.5...2.5 mm² for stranded cable(s)
Wire Stripping Length	8 mm
Material	PC/ABS
Protection Type	Short time short-circuit protection
Fixing Mode	By screws
Type Of Packing	Flow-pack
Product Compatibility	Mobile/tablet Mac iOS Mobile/tablet Android Mobile/tablet Windows

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	87 mm
Width	87 mm
Depth	42 mm
Embedding Depth	30.8 mm
Net Weight	0.03 kg

Environment

Standards	EN 60950-1 EN 60335-1 EN 61558-1
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive 2009/125/EC - ecodesign
Product Certifications	NEMKO SEMKO FIMKO
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	0.5 cm
Package 1 Length	12 cm
Package 1 Weight	118 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	12.2 cm
Package 2 Width	19.4 cm
Package 2 Length	26 cm
Package 2 Weight	790 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	20
Package 3 Height	325.8 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.64 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins