

Product data sheet

Specifications



Renova Surface Switch 2-pole screwless with rocker marked with 1 and 0 white

WDE015807

Main

Range	Renova
Product Or Component Type	Switch
Device Application	Light control
Device Presentation	Complete product
Colour	White (RAL 9010)
Quantity Per Set	Set of 5
Switch Function	2-pole

Complementary

Technology Type	Electromechanical
Rated Current	16 AX
[Ue] Rated Operational Voltage	250 V AC
Connections - Terminals	Screwless terminals
Number Of Loop Terminals	2
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Device Mounting	Surface
Number Of Rocker	1
Switch Pattern	[2]
Actuator	Rocker
Material	PC: cover PC 10 % GF: bottom-plate PC/ABS: rocker
Surface Finish	Cover plate: glossy Cover frame: matt
Fixing Mode	By screw
Diameter	70.0 mm
Embedding Depth	0.0 mm
Projecting Depth	27.0 mm
Ip Degree Of Protection	IP20 IP21 when cable is coming from below
Product Certifications	CE FIMKO NEMKO SEMKO

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60669-1
-----------	------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	6.9 cm
Package 1 Length	6.8 cm
Package 1 Weight	60 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.8 cm
Package 2 Width	8.6 cm
Package 2 Length	22.8 cm
Package 2 Weight	352 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	60
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.74 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✔</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✔</div><div>Mercury Free</div></div>	
<div><div>✔</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
Eu Rohs Directive	<div>Compliant</div> <div>EU RoHS Declaration</div>
China Rohs Regulation	<div>China RoHS declaration</div> <div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div>
Weee	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div>