

# Product data sheet

Specifications



Socket-outlet, Exxact, mechanism with fixing frame, 2P + E, 16A, Schuko, with shutter,transparent

WDE004493

## Main

|                                |   |
|--------------------------------|---|
| Range                          | Exxact  |
| Product Or Component Type      | Socket-outlet   |
| Device Application             | Power supply  |
| Device Presentation            | Mechanism with fixing frame   |
| Socket Number                  | 1   |
| Outlet Standard                | CEE 7/3   |
| Outlet Standard                | Schuko  |
| [Ue] Rated Operational Voltage | 250 V   |
| Network Type                   | AC  |
| Provided Equipment             | Including 4 inlays (6 colours + 1 pattern) that can easily be changed |
| Colour Tint                    | Transparent   |
| Quantity Per Set               | Set of 5  |

## Complementary

|                              |   |
|------------------------------|---|
| Device Mounting              | Flush   |
| Outlet Poles Configuration   | 2P + E  |
| Rated Current                | 16 A  |
| Cover Type                   | With shutter  |
| Function Available           | Possibility to put wallpaper, pictures etc instead of the inlays                              |
| Fixing Mode                  | By screws   |
| Connections - Terminals      | Screw terminals   |
| Shape Of Screw Head          | Pozidriv No 1 and combi   |
| Clamping Connection Capacity | 1 x 1.5...2 x 2.5 mm² for solid cable(s)<br>1 x 1.5...2 x 2.5 mm² for solid stranded cable(s) |
| Material                     | ASA + PC  |
| Depth                        | 39.8 mm   |
| Embedding Depth              | 28 mm   |
| Height                       | 71 mm   |
| Width                        | 71 mm   |
| Projecting Depth             | 11.8 mm   |

## Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                         |  |
|-------------------------|--|
| Ip Degree Of Protection | IP20   |
| Standards               | SS 4280834<br>DIN VDE 0620-1<br>NEK 502:2006<br>SFS 5610:2004<br>IEC 60884-1 |
| Product Certifications  | NEMKO<br>SEMKO<br>FIMKO  |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 4.700 cm  |
| Package 1 Width              | 7.200 cm  |
| Package 1 Length             | 7.400 cm  |
| Package 1 Weight             | 78.000 g  |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 10        |
| Package 2 Height             | 9.400 cm  |
| Package 2 Width              | 18.000 cm |
| Package 2 Length             | 27.000 cm |
| Package 2 Weight             | 908.000 g |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Sustainable Packaging   Transparency   RoHS/REACH

## Resource performance

✓ Sustainable Packaging

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope)                 |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | No need of specific recycling operations  |