


Product data sheet

Specifications



3 Socket-outlet, Exxact, mechanism with fixing frame, 2P, 2.5A, universal, with shutter, metallic

WDE004679

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Exxact
Product Or Component Type	Socket-outlet
Device Application	Power supply
Device Presentation	Mechanism with fixing frame
Socket Number	3
Outlet Standard	Universal
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Colour Tint	Metallic
Quantity Per Set	Set of 5

Complementary

Device Mounting	Flush
Outlet Poles Configuration	2P
Rated Current	2.5 A
Cover Type	With shutter
Fixing Mode	By screws
Connections - Terminals	Screw terminals
Number Of Loop Terminals	2
Shape Of Screw Head	Pozidriv No 1 and combi
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	ASA + PC
Depth	40.8 mm
Embedding Depth	29 mm
Height	70.8 mm
Width	70.8 mm
Projecting Depth	11.8 mm

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	SFS 5610:2004
	IEC 60884-1
	SS 4280834
	NEK 502:2006
	IEC 60884-2-2
Product Certifications	FIMKO
	NEMKO
	SEMKO

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7 cm
Package 1 Length	7 cm
Package 1 Weight	80 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.5 cm
Package 2 Width	8.5 cm
Package 2 Length	22.5 cm
Package 2 Weight	454 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations