


Product data sheet

Specifications



die-cast empty control station,
XAPG, grey, Ø22, 80x175mm front
plate, 4 cut-outs

XAPG3504

! Discontinued

! Discontinued on: Jun 30, 2022

! End-of-service on: Jul 28, 2022

Main

| | |
|-----------------------------|--|
| Range Of Product | Harmony XAP |
| Product Or Component Type | Die-cast empty control station |
| Device Short Name | XAPG |
| Product Destination | For Ø 22 mm control and signalling units |
| Product Front Plate Size | 80 x 175 mm |
| Usable Depth | 74.5 mm |
| Number Of Cut-Out | 4 cut-outs |
| Colour Of Base Of Enclosure | Grey (RAL 7032) |
| Colour Of Cover | Grey (RAL 7032) |
| Material | Zinc alloy |
| Product Mounting | Flush mounting |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |

Complementary

| | |
|-------------------------|---|
| Number Of Vertical Rows | 1 |
| Cable Entry | 18 mm 1 hole with blanking plug for cable gland 18 mm 1 hole without blanking plug for cable gland |
| Net Weight | 1.14 kg |
| Compatibility Code | XAPG |

Environment

| | |
|---------------------------------------|--|
| Protective Treatment | TH |
| Ambient Air Temperature For Storage | -40...70 °C |
| Ambient Air Temperature For Operation | -25...70 °C |
| Electrical Shock Protection Class | Class I conforming to IEC 60536 Class I conforming to NF C 20-030 |

Packing Units

| | |
|------------------------------|-------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 15 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|---------|
| Package 1 Width | 30 cm |
| Package 1 Length | 40 cm |
| Package 1 Weight | 1.14 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|---------------------------|--|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |