

Product data sheet

Specifications



Control station, Harmony XAW, metal, Emergency stop function, key release, 1 mushroom head push button 40mm, red, 1NC + 1NC, ATEX

XAWF188EX

Main

Range Of Product	Harmony XAW
Product Or Component Type	Complete control station
Device Short Name	XAWF
Control Station Application	Emergency stop function
Material	Metal
Reset	Key release
Control Station Composition	1 mushroom head Ø 40 mm push-button, red, trigger action 1 NC + 1 NC

Complementary

Colour Of Base Of Enclosure	Black
Colour Of Cover	Black
Cable Entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	77 mm
Height	80 mm
Net Weight	0.830 kg
Marking	Ex tb IIIC T85°C Db IP65
Mechanical Durability	300000 cycles
Short-Circuit Protection	10 A cartridge fuse type gG
[Ie] Rated Operational Current	3 A at 240 V, AC-15, A600 6 A at 120 V, AC-15, A600 0.1 A at 600 V, DC-13, Q600 0.27 A at 250 V, DC-13, Q600 0.55 A at 125 V, DC-13, Q600 1.2 A at 600 V, AC-15, A600

Environment

Ambient Air Temperature For Operation	-20...60 °C
Overvoltage Category	I conforming to IEC 60536
Ip Degree Of Protection	IP65 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60079-0:2009
	EN 60079-31:2009
	IEC 60947-5-4
	IEC 61000-6-2
	IEC 60947-1
	IEC 60947-5-1
	IEC 60079-0:2007
	IEC 60079-31:2008
	IEC 60947-5-5
	ISO 13850
Directives	94/9/EC - ATEX directive
Dust Zone	Zone 21 - 22
Product Certifications	INERIS 04ATEX0023X

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration