

# Product data sheet

Specifications



## Cover frame, Exxact Combi, 2 gangs, metallic

WDE004802

### Main

Range	Exxact
Aesthetic Name	Combi
Product Or Component Type	Cover frame
Number Of Gangs	2 gangs
Colour Tint	Metallic
Quantity Per Set	Set of 5

### Complementary

Device Mounting	Flush Surface
Material	ABS (acrylonitrile butadiene-styrene)
Standards	IEC 60884-1 EN 60669-1
Product Certifications	CE FIMKO
Ip Degree Of Protection	IP20
Height	158 mm
Width	87 mm
Depth	11.6 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.600 cm
Package 1 Width	9.300 cm
Package 1 Length	15.900 cm
Package 1 Weight	46.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	8.100 cm
Package 2 Width	16.300 cm
Package 2 Length	10.800 cm
Package 2 Weight	264.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	CAR
Number Of Units In Package 3	30
Package 3 Height	12.600 cm
Package 3 Width	39.600 cm
Package 3 Length	29.800 cm
Package 3 Weight	1.902 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations