

# Product data sheet

Specifications



2 Socket-outlet, Exxact, complete product, 2P + E, 16A, Schuko, with shutter,white

WDE008285

## Main

Range	Exxact
Product Or Component Type	Socket-outlet
Device Application	Power supply
Device Presentation	Complete product
Socket Number	2
Outlet Standard	CEE 7/3
Outlet Standard	Schuko
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Colour Tint	White (RAL 9003)

## Complementary

Device Mounting	Flush
Outlet Poles Configuration	2P + E
Rated Current	16 A
Cover Type	With shutter
Fixing Mode	By claw kit
Connections - Terminals	Screw terminals
Number Of Loop Terminals	2
Shape Of Screw Head	Pozidriv No 1 and combi
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for solid stranded cable(s)
Material	PC (polycarbonate) PC
Depth	44.2 mm
Embedding Depth	22.4 mm
Height	100 mm
Width	85 mm
Projecting Depth	21.8 mm

## Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	NEK 502:2006 SFS 5610:2004 IEC 60884-1 DIN VDE 0620-1 SS 4280834
Product Certifications	SEMKO FIMKO NEMKO

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.600 cm
Package 1 Length	17.600 cm
Package 1 Weight	138.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	13.100 cm
Package 2 Width	25.300 cm
Package 2 Length	17.100 cm
Package 2 Weight	778.000 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	30
Package 3 Height	34.800 cm
Package 3 Width	40.200 cm
Package 3 Length	29.600 cm
Package 3 Weight	5.090 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations