

Product data sheet

Specifications



Support tube, Harmony XVM, with metal bracket l=250mm, aluminium

XVMZ03T

Main

| | |
|---------------------------------------|---|
| Range Of Product | Harmony XVM |
| Accessory / Separate Part Designation | Ø 20 mm aluminium support tube with metal bracket |
| Product Or Component Type | Support tube |
| Accessory / Separate Part Category | Mounting and fixing accessories |
| Accessory / Separate Part Destination | Beacons and indicator banks Ø 45 mm |

Complementary

| | |
|--------------------------------|---------------------------|
| Accessory / Separate Part Type | Support tube with bracket |
| Product Compatibility | XVM. |
| Colour | Aluminium |
| Height Under Base Unit | 263 mm |
| Length | 250 mm |
| Net Weight | 0.242 kg |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 29.1 cm |
| Package 1 Width | 3.5 cm |
| Package 1 Length | 6.1 cm |
| Package 1 Weight | 243.0 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 15 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 4.135 kg |
| Unit Type Of Package 3 | PAL |
| Number Of Units In Package 3 | 240 |
| Package 3 Height | 60.0 cm |
| Package 3 Width | 80.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|-----------|
| Package 3 Length | 240.0 cm |
| Package 3 Weight | 147.12 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free


✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Dimensions and Mounting



| Support tube length | | b1 (tube + plate) | | b2 (height under base unit) | |
|---------------------|------|-------------------|-------|-----------------------------|-------|
| mm | in. | mm | in. | mm | in. |
| 250 | 9.84 | 283 | 11.14 | 256 | 10.08 |

Mounting and Clearance

Panel Cut-Out

