

Product data sheet

Specifications



Multisound siren, Harmony XVS,
white colour, 106dB, 2tones, 230V
AC

XVS10MMW

Main

Range Of Product	Harmony XVS
Product Or Component Type	Siren
Device Short Name	XVS
Colour	White
Signalling Type	2 tones siren
[Us] Rated Supply Voltage	230 V AC
Noise Level	106 dB (continuous or intermittent tone) at 1 m

Complementary

Material	PC: body
Net Weight	1 kg
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	4 kV
Current Consumption	40 mA at 230 V
Clamping Connection Capacity	<= 1 x 1.5 mm²
Electrical Connection	Cable: 6.5...8.5 mm
Width	114 mm
Height	114 mm
Depth	153.2 mm

Environment

Standards	IEC 60947-1 IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-30...50 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP53

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	19.500 cm
Package 1 Width	14.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	1.242 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	11.109 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	53.960 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Siren

Dimensions

