


Product data sheet

Specifications



Control station, Harmony XAW,
metal, start function, 1 flush push
button 40mm, green, 1NO, ATEX

XAWF100EX

Main

Range Of Product	Harmony XAW
Product Or Component Type	Complete control station
Device Short Name	XAWF
Control Station Application	Start function
Material	Metal
Control Station Composition	1 flush push-button, green, spring return 1 NO

Complementary

Colour Of Base Of Enclosure	Black
Colour Of Cover	Black
Cable Entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	77 mm
Height	80 mm
Net Weight	0.830 kg
Marking	Ex tb IIIC T85°C Db IP65
Mechanical Durability	5000000 cycles
Short-Circuit Protection	10 A cartridge fuse type gG
[Ie] Rated Operational Current	3 A at 240 V, AC-15, A600 conforming to IEC 60947-5-1 6 A at 120 V, AC-15, A600 conforming to IEC 60947-5-1 0.1 A at 600 V, DC-13, Q600 conforming to IEC 60947-5-1 0.27 A at 250 V, DC-13, Q600 conforming to IEC 60947-5-1 0.55 A at 125 V, DC-13, Q600 conforming to IEC 60947-5-1 1.2 A at 600 V, AC-15, A600 conforming to IEC 60947-5-1

Environment

Ambient Air Temperature For Operation	-20...60 °C
Overvoltage Category	I conforming to IEC 60536
Ip Degree Of Protection	IP65 conforming to IEC 60529
Standards	IEC 60079-0:2009 EN 60079-31:2009 IEC 60947-5-4 IEC 61000-6-2 IEC 60947-1 IEC 60947-5-1 IEC 60079-0:2007 IEC 60079-31:2008

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Directives	94/9/EC - ATEX directive
Dust Zone	Zone 21 - 22
Product Certifications	INERIS 04ATEX0023X

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	13.5 cm
Package 1 Length	23.5 cm
Package 1 Weight	866.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	4
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.854 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration