

Product data sheet

Specifications



Single block for test light function,
Harmony XB4, 12 and 24V AC DC,
24...120V AC DC

ZBZG156

Main

Range Of Product	Harmony XB4 Harmony XB5
Product Or Component Type	Block for test light
Product Compatibility	Integral LED BA 9s
Light Block Type	Single block for test light function
[Us] Rated Supply Voltage	12 V AC/DC 24 V AC/DC 24...120 V AC/DC
Electrical Connection	1 wire

Complementary

Material	Plastic
Electrical Shock Protection Class	Class I for Harmony XB4 conforming to IEC 60536 Class II for Harmony XB5 conforming to IEC 60536
Net Weight	0.01 kg

Environment

Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Standards	UL 508 IEC 60947-5-5 IEC 60947-1 IEC 60947-5-4 IEC 60947-5-1 IEC 60947-5-5 IEC 60947-5-4 CSA C22.2 No 14 IEC 60947-1 IEC 60947-5-1 JIS C 4520
Product Certifications	LROS (Lloyds register of shipping) UL listed DNV BV CSA GL
Vibration Resistance	5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	30 gn for 18 ms conforming to IEC 60068-2-27 50 gn for 11 ms conforming to IEC 60068-2-27

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.8 cm
Package 1 Length	5.2 cm
Package 1 Weight	18.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	165
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.65 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Connections and Schema

Wiring Diagram

