



LINERGY BW 3P INSULATED B.BAR 400A L1400

04118

Discontinued on: 15 Jun 2023

(!) Discontinued

Main

Range	Linergy	
Range Of Product	Linergy	
Product Or Component Type	Busbar	
Product Name	Linergy BW	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure	
Ip Degree Of Protection	IPxx B	
Busbar Description	Insulated bar	
Quantity Per Set	Set of 1	

Complementary

Poles Description	3P
Installation Direction	Vertical, operating position: rear
Installation Description	Cubicle - width 650 mm Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
[Ui] Rated Insulation Voltage	750 V
[Uimp] Rated Impulse Withstand Voltage	8 kV
[le] Rated Operational Current	400 A
[Icw] Rated Short-Time Withstand Current	20 kA (1 s)
[lpk] Rated Peak Withstand Current	52.5 kA
I ² T On Activation	400000 kA².s
Permissible Current	400 A
Length	1400 mm
Net Weight	7.1 kg
Type Of Busbar Connection	M6 threaded hole
Connection Pitch	Connection each 25 mm

Environment

Standards	IEC 61439-1 IEC 61439-2	
Product Certifications	ASEFA	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	13.0 cm
Package 1 Length	152.5 cm
Package 1 Weight	7.1 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	54
Package 2 Height	45.0 cm
Package 2 Width	200.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	383.4 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins