

Product data sheet

Specifications



Limit switch head, Limit switches XC Standard, ZCKD, thermoplastic round rod lever 6 mm L = 200 mm

ZCKD59

Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKS XCKM XCKL

Associated body	ZCKS5H29 ZCKMD31H7 ZCKLD35H7 ZCKMD39H7 ZCKMD35 ZCKS9H29 ZCKS1H29 ZCKL6H7 ZCKS5 ZCKS1 ZCKLD35 ZCKL5H7 ZCKS6H29 ZCKM5H7 ZCKSD35 ZCKLD31 ZCKM8 ZCKMD37 ZCKM7H29 ZCKS6 ZCKS7H29 ZCKM1H7 ZCKS9 ZCKS2H29 ZCKM8H29 ZCKLD37 ZCKLD39H7 ZCKMD39H29 ZCKSD35H29 ZCKM6H29 ZCKMD31 ZCKLD39 ZCKSD39 ZCKMD31H29 ZCKM9 ZCKLD37H7 ZCKL5 ZCKM1H29 ZCKM6 ZCKS2 ZCKSD39H29 ZCKS8 ZCKL6 ZCKMD35H7 ZCKSD31H29 ZCKS7 ZCKSD31
-----------------	--

ZCKM6H7
 ZCKM5
 ZCKMD39
 ZCKM9H29
 ZCKMD35H29
 ZCKL1H7
 ZCKL7
 ZCKM7H7
 ZCKL8
 ZCKM8H7
 ZCKL7H7
 ZCKL1
 ZCKSD37
 ZCKL8H7
 ZCKLD31H7
 ZCKSD37H29
 ZCKM5H29
 ZCKM1
 ZCKS8H29
 ZCKMD37H29
 ZCKMD37H7
 ZCKM7

Movement of operating head	Rotary
Type of operator	Rod lever spring return glass fiber (round rod 6 mm, L = 200 mm)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Plastic

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	6.8 cm
Package 1 Length	22.1 cm
Package 1 Weight	104.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	18
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.359 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty 18 months

Recommended replacement(s)