Product datasheet

Specifications







03402

- ! Discontinued on: 14 Jan 2022
- ! End-of-service on: 30 Dec 2022

! Discontinued

Price: 838.60 ZAR

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Rail
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P
Type Of Rail	Adjustable Modular
Installed Device	TeSys: fixed GV2L TeSys: fixed GV2P TeSys: fixed GV3 ComPact: fixed NG160 without earth leakage protection - control: toggle ComPact: fixed NG160 NA without earth leakage protection - control: toggle ComPact: fixed NG160 with earth leakage protection - control: toggle Altistart: ATS01N Altistart: ATS01N103/106FT TeSys: fixed D or K contactors <= 40 A - horizontal installation TeSys: fixed GV2 + D or K contactors <= 40 A - horizontal installation TeSys: fixed TeSys U - horizontal installation PowerLogic: PM5500 PowerLogic: iEM3000 PowerLogic: PM3000 PowerLogic: PM5563RD ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles Description	9 x 3P: fixed GV2L 9 x 3P: fixed GV2P 7 x 3P: fixed GV3 1 x 3P: fixed NG160 1 x 4P: fixed NG160 1 x 3P: fixed NG160 NA 1 x 4P: fixed NG160 NA 9 x 4P: fixed D or K contactors <= 40 A horizontal installation 9 x 3P: fixed GV2 + D or K contactors <= 40 A horizontal installation 9 x 3P: fixed TeSys U horizontal installation 1 x 3P or 4P: fixed NSXm vertical installation

Complementary

Installation Description	Cubicle - width 650 mm depth 400 mm
Enclosure Nominal Height	2000 mm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Number Of Vertical Modules [50	5 module(s): ATS01N in 650 mm Widecubicle	
Mm]	6 module(s): ATS01N in 650 mm Widecubicle	
	4 module(s): ATS01N103/106FT in 650 mm Widecubicle	
	3 module(s): D or K contactors <= 40 A, direct in 650 mm Widecubicle	
	5 module(s): GV2 + D or K contactors <= 40 A, direct in 650 mm Widecubicle	
	3 module(s): GV2L, direct in 650 mm Widecubicle	
	3 module(s): GV2P, direct in 650 mm Widecubicle	
	5 module(s): GV3, direct in 650 mm Widecubicle	
	4 module(s): iEM3000 in 650 mm Widecubicle	
	5 module(s): NG160 without earth leakage protection, direct in 650 mm Widecubicle	
	5 module(s): NG160 NA without earth leakage protection, direct in 650 mm	
	Widecubicle	
	8 module(s): NSXm without earth leakage protection, direct in 650 mm Widecubicle	
	4 module(s): PM3000 in 650 mm Widecubicle	
	3 module(s): PM5500 in 650 mm Widecubicle	
	3 module(s): PM5563RD in 650 mm Widecubicle	
	5 module(s): TeSys U, direct in 650 mm Widecubicle	
	4 module(s): TeSys U, direct in 650 mm Widecubicle	
	5 module(s): NG160 with earth leakage protection , direct in 650 mm Widecubicle	
	8 module(s): NSXm with earth leakage protection , direct in 650 mm Widecubicle	
9 Mm Pitches	48	
Quantity Per Set	Set of 1	
Height	30 mm	
Width	563 mm	
Depth	325 mm	
Net Weight	0.86 kg	
Colour	Natural	
Material	Metal	
Environment		
 Standards	IEC 61439-1	
ao	IEC 61439-1	
	120 01 100 2	
Product Certifications	ASEFA	
D 1.1		
Packing Units		

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	5 cm
Package 1 Length	52 cm
Package 1 Weight	850 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	
China Rons Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	
Environmental Disclosure	Product Environmental Profile
Circularity Profile	Find of Utility Information
On outainty i forme	End of Life Information