Product datasheet

Specifications



LINERGY FM 3P DIS.BLOCK 200A 24M 42HOLES

04013

() Discontinued

() Discontinued on: 15 Jun 2023

Price: 2,273.46 ZAR

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Device feeder
Product Name	Linergy FM
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure Prisma Prisma PH enclosure
Product Compatibility	Spacial enclosures
Ip Degree Of Protection	IPxx B

Complementary

oompiomontary	
Mounting Support	Plain backplate DIN rail Slotted backplate
Installed Device	modular device
Poles Description	3P
[Ue] Rated Operational Voltage	690 V AC
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ie] Rated Operational Current	200 A
[In] Rated Current	200 A at 40 °C
[Ipk] Rated Peak Withstand Current	20 kA
I ² T On Activation	6700000 A².s
Connections - Terminals	Supply: crimped lug50 mm ² Supply: flexible bars, 20 x 3 mm Distribution: quick-connect terminal strips (phase) , 12 x 410 mm ² (flexible) Distribution: quick-connect terminal strips (phase) , 12 x 410 mm ² (rigid) Distribution: quick-connect terminal strips (neutral) , 18 x 410 mm ² (flexible) Distribution: quick-connect terminal strips (neutral) , 18 x 410 mm ² (rigid)
9 Mm Pitches	48
Total Number Of 18 Mm Modules	24
Net Weight	1.32 kg
Colour	Anthracite grey (RAL 7016)

Environment

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma IEC 60947-7-1
Product Certifications	ASEFA

Packing Units

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins