
# **Product datasheet**

Specifications





04146

() Discontinued on: 15 Jun 2023

① Discontinued

N /		-
IVI	ai	n

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Connection
Product Name	Linergy BW
Product Name	Prisma Prisma P enclosure Prisma Prisma G enclosure Linergy Linergy BW busbar
Provided Equipment	With connection
Standards	IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma
Product Certifications	ASEFA

## Complementary

Cubicle-Device Connection	Linergy BS busbar
Poles Description	4P
Installation Description	Floor-standing enclosure - width 600mm Wall-mounted enclosure - width 600mm Floor-standing enclosure - width 850mm Pack enclosure - width 550mm Cubicle - width 600mm
Installed Device	Multi9: NG125 ComPact: NG160 ComPact: INS160
[Ie] Rated Operational Current	160 A
[In] Rated Current	160 A
Length	250 mm
Net Weight	0.6 kg
Quantity Per Set	Set of 4

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	10.0 cm
Package 1 Length	30.0 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Package 1 Weight	600.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.46 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	30.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	24.0 kg

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile