Product datasheet

Specifications





4 THREADED BARS 630A L1400/ LINERGY BS BB

04174

! Discontinued on: 15 Jun 2023

Price: 17,689.52 ZAR

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Copper busbar
Product Name	Linergy BS
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure
Busbar Description	Flat bar
Quantity Per Set	Set of 4

Complementary

Installation Direction	Vertical, operating position: rear
Installation Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm
[le] Rated Operational Current	630 A
[lpk] Rated Peak Withstand Current	55 kA
I ² T On Activation	625000 kA².s
Busbar Cross Section	32 x 8 mm
Length	1400 mm
Net Weight	12.54 kg
Type Of Busbar Connection	M6 threaded hole
Connection Pitch	Connection each 25 mm
Support Thickness	8 mm

Environment

Standards	IEC 61439-1 IEC 61439-2	
Product Certifications	ASEFA	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Package 1 Width	13.0 cm
Package 1 Length	150.0 cm
Package 1 Weight	12.45 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	48
Package 2 Height	21.0 cm
Package 2 Width	200.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	601.92 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive

	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Compliant