
Product datasheet

Specifications

Green Premium™



LINERGY TA AUXIL.TERM.BLK 10 IN/20 OUT

04228

() Discontinued on: 15 Jun 2023

Price: 492.34 ZAR

Main

Range	Linergy	
Range Of Product	Linergy	
Product Or Component Type	ype Terminal block	
Product Name	Linergy TA	
Accessory / Separate Part Category	Connection accessory	
Range Compatibility	Linergy Linergy TA auxiliary connector Prisma Prisma G enclosure Prisma Prisma P cubicle	
Product Compatibility	Auxiliary connection	

Complementary

oompiementai y	
Enclosure/Cubicle Description	Cubicle Floor-standing enclosure Wall-mounted enclosure
[Ie] Rated Operational Current	12 A (40 °C) at 250 V AC conforming to IEC 20 A (40 °C) at 300 V AC conforming to UL
Tightening Torque	0.50.6 N.m
onnections - Terminals Input: screw terminal 10 pin(s) 0.24 mm ² rigid without cable end Output: removable screw terminal block 20 pin(s) 0.24 mm ² flexible with cable	
Conductor Material	Copper
Quantity Per Set	Set of 1
Height	50 mm
Width	65 mm
Depth	50 mm
Net Weight	0.12 kg
Colour	Light grey (RAL 7035)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	5.0 cm
Package 1 Length	5.0 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Package 1 Weight	110.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	50
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.34 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information