


Product datasheet

Specifications



PLAIN HORIZONTAL FLAT BAR LINERGY BS 80X10 L2000

04548

⚠ Discontinued on: 17 Jan 2022

⚠ End-of-service on: 17 Dec 2022

⚠ Discontinued

Price: 14,190.31 ZAR

Main

Range	Linery
Range Of Product	Linery
Product Or Component Type	Copper busbar
Product Name	Linery BS
Range Compatibility	Prisma Prisma P enclosure
Busbar Description	Flat bar
Quantity Per Set	Set of 1

Complementary

Installation Direction	Horizontal, operating position: top Horizontal, operating position: bottom
Installation Description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ie] Rated Operational Current	1800 A at 35 °C
[Icw] Rated Short-Time Withstand Current	40 kA (1 s) for 2 supports 65 kA (1 s) for 3 supports 75 kA (1 s) for 4 supports
Permissible Current	1800 A at 35 °C: <= IP31 1600 A at 35 °C: > IP31
Busbar Cross Section	80 x 10 mm
Length	2000 mm
Height	150 mm
Net Weight	14.72 kg
Type Of Busbar Connection	Without hole
Support Thickness	10 mm

Environment

Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA

Packing Units

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information