Product datasheet

Specifications





(!) Discontinued

WALL-MOUNTED ENCLOSURE W600 27M PRISMA G IP30

08109

! Discontinued on: 15 Jun 2023

Price: 7,622.36 ZAR

Main

Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Enclosure	
Device Application	Low voltage electrical distribution	
Enclosure Type	Functional enclosure delivered in kit form	
Enclosure/Cubicle Description	Wall-mounted enclosure - width 600 mm	
Enclosure Mounting	Surface Flush with kit	
Additional Information	Can be combined side by side and one on top of another	
Type Of Front Plate	Without to be ordered separately	
Number Of Vertical Modules [50 Mm]	27	
Number Of 18 Mm Modules Per Row	24	
Standards	IEC 62208 IEC 61439-1 IEC 61439-2	

Complementary

[Ui] Rated Insulation Voltage	1000 V on main rear busbars conforming to IEC 61439-2
Network Frequency	50/60 Hz
[In] Rated Current	630 A at 40 °C conforming to IEC 61439-2
[Icw] Rated Short-Time Withstand Current	25 kA 1 s conforming to IEC 61439-2
[lpk] Rated Peak Withstand Current	53 kA conforming to IEC 61439-2
Electrical Insulation Class	Class I
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	1380 mm
Depth	205 mm
Net Weight	21.34 kg
Quantity Per Set	Set of 1

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Environment

Ip Degree Of Protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy
Ik Degree Of Protection	IK07 without door conforming to EN/IEC 62262 IK08 with door
Mechanical Robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	64.000 cm
Package 1 Length	143.000 cm
Package 1 Weight	21.150 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	103.000 cm
Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	426.800 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile