Product datasheet

Specifications





PLAIN DOOR+FRAME W600 11M PRISMA G IP55

08323

Discontinued on: 15 Jun 2023

! Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Door
Range Compatibility	Prisma Prisma G enclosure
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Type Of Door	Plain
Ip Degree Of Protection	IP55

Complementary

•	
Installation Description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door Opening Side	Reversible
Number Of Locks	3
Door Opening Angle	180 °
Number Of Vertical Modules [50 Mm]	11
Enclosure Material	Treated sheet steel
Quantity Per Set	Set of 1
Height	650 mm
Width	600 mm
Depth	26 mm
Net Weight	10.94 kg
Surface Finish	Smooth Matt
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-2 IEC 61439-1
Protective Treatment	Flectrophoresis treatment and hot-polymerised polyester epoxy powder

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.3 cm
Package 1 Width	60.0 cm
Package 1 Length	64.2 cm
Package 1 Weight	10.664 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	20
Package 2 Height	85.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	218.8 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile